

**An 'absorber' that
looks like it works well.
And can.**



MSB-1

MICROSORBER

"Microsorber" stands for micro shock absorber, which eliminates the howling dramatically from your stereo and assures clean musical sound reproduction, without any microphonic noise or distortions.

When musical sound is reproduced on the turn table, it goes out from the speaker and is transmitted through the wall or the floor. Then it is conveyed to the needle of the cartridge. Via speaker, wall or floor, needle and amplifier, this movement is endless. As the result of this movement, the howling — unpleasant vibration — occurs. It's not only unpleasant to hear, but cracks the needle or the record. The howling occurs frequently when broadcasting in the frequency range between 50 to 200 Hz with the highly-qualified speaker. As the diagram shows, low frequency range is transmitted.

"Microsorber", which we have developed for clear reproduction, is made of superior rubber and felt. Thanks to its excellent material, it wouldn't change in quality by the long duration or the heavy weight. Moreover, it can be used for any type of the turn table.


It's available for "Microsorber" to support 9 lbs. per unit. As the distribution of weight in turn table is not equal, you can operate the height-adjusting knob for keeping the turn table horizontally. Its adjustable height is 3/8 inch. And you can keep the turn table horizontal by using a level meter with the height-adjusting knob of the "Microsorber".

MICRO

MANUFACTURER, SPECIALISTS IN HIGH FIDELITY PRODUCTS



This diagram shows the difference between A and B.



How to use

- 1) Place them under the 4 corners of the turn table, or you may use them upside down.
- 2) Because of the unequal distribution of weight of the turn table, adjust it equally by operating the height-adjusting knob. It's better way for adjusting more horizontally to utilize a level with the microsorbers, which adjust up to down 3/8 inch. by graduations.
- 3) Use them horizontally to the floor. If not, the height-adjusting knob would be disturbed by the floor and the faculty of them would be extremely spoiled.
- 4) They support 9 lbs. of weight per every unit. When exceeded, use more than 4 for enough stability.

SPECIFICATIONS

Height Adjustable Range	: Up to 3/8 inch
Supportable Weight Per pc.	: 9 lbs.
Dimensions	: 2-3/16" dia 1-3/4" min. (H)
Net Weight	: 0.6 lbs. (4 pcs. per case)

